

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Ball and Condenser Lenses](#)

B270 Half-Ball Lenses



- Available in Truncated and Extended Geometries
- High Transmission in the Visible and NIR
- Ideal for Cost Sensitive Applications

Common Specifications

Optical Properties

Substrate: B270	Coating: Uncoated
Wavelength Range (nm): 360 - 2700	Index of Refraction (n_d): 1.523

Technical Information

Products

Dia. (mm)	Substrate	Type	CT (mm)	Coating	Stock Number	Price	Buy
3.00	B270	Half-Ball Lens	1.50	Uncoated	#21-896	S\$51.80 Volume Pricing	3 In Stock
3.00	B270	Half-Ball Lens	1.20	Uncoated	#21-897	S\$51.80 Volume Pricing	6 In Stock
3.00	B270	Half-Ball Lens	1.80	Uncoated	#21-898	S\$51.80 Volume Pricing	6 In Stock
4.00	B270	Half-Ball Lens	2.00	Uncoated	#21-899	S\$51.80 Volume Pricing	4 In Stock
4.00	B270	Half-Ball Lens	1.70	Uncoated	#21-900	S\$51.80 Volume Pricing	11 In Stock
4.00	B270	Half-Ball Lens	2.30	Uncoated	#21-901	S\$51.80 Volume Pricing	8 In Stock
5.00	B270	Half-Ball Lens	2.50	Uncoated	#21-902	S\$56.00 Volume Pricing	20+ In Stock
5.00	B270	Half-Ball Lens	2.20	Uncoated	#21-903	S\$56.00 Volume Pricing	4 In Stock
5.00	B270	Half-Ball Lens	2.80	Uncoated	#21-904	S\$56.00 Volume Pricing	4 In Stock
6.00	B270	Half-Ball Lens	3.00	Uncoated	#21-905	S\$56.00 Volume Pricing	20+ In Stock
6.00	B270	Half-Ball Lens	2.70	Uncoated	#21-906	S\$56.00 Volume Pricing	5 In Stock
6.00	B270	Half-Ball Lens	3.30	Uncoated	#21-907	S\$56.00 Volume Pricing	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com