

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Industrial and Pointing Lasers](#)

USB Powered Alignment Laser Diode Modules



- USB Powered and Controllable via Computer
- Software Allows for Modulation and Output Power Control
- Available in Wavelengths From 405nm to 940nm

Common Specifications

General			
Laser Class - CDRH:		IIIB	
Physical & Mechanical Properties			
Housing Diameter (mm):		19	
Length (mm):		90.00	
Optical Properties			
Beam Diameter (mm):		4.5	
Beam Divergence (mrad):		Adjustable	
Electrical			
Modulation Frequency (kHz):		0.1 - 50	
Hardware & Interface Connectivity			
Operating Voltage (V):		5	Power Supply: USB 5V ±0.5V 1A
Environmental & Durability Factors			
Operating Temperature (°C):		10 - 35	

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Stock Number	Price	Buy
405.00	10	#26-930	S\$784.00 Volume Pricing	2 In Stock
405.00	20	#26-931	S\$875.00 Volume Pricing	1 In Stock
405.00	50	#26-932	S\$966.00 Volume Pricing	5 In Stock
450.00	10	#26-933	S\$742.00 Volume Pricing	1 In Stock
450.00	20	#26-934	S\$833.00 Volume Pricing	1 In Stock
450.00	50	#26-935	S\$924.00 Volume Pricing	4 In Stock
488.00	10	#26-936	S\$833.00 Volume Pricing	5 In Stock
488.00	20	#26-937	S\$924.00 Volume Pricing	5 In Stock
520.00	10	#26-938	S\$742.00 Volume Pricing	4 In Stock
520.00	20	#26-939	S\$833.00 Volume Pricing	3 In Stock
520.00	50	#26-940	S\$924.00 Volume Pricing	7 In Stock
637.00	10	#26-941	S\$645.40 Volume Pricing	4 In Stock
637.00	20	#26-942	S\$742.00 Volume Pricing	1 In Stock
637.00	50	#26-943	S\$833.00 Volume Pricing	3 In Stock
660.00	10	#26-944	S\$742.00 Volume Pricing	3 In Stock
660.00	20	#26-945	S\$833.00 Volume Pricing	1 In Stock
660.00	50	#26-946	S\$924.00 Volume Pricing	4 In Stock

685.00	10	#26-947	S\$1,106.00 Volume Pricing	2 In Stock
685.00	20	#26-948	S\$1,204.00 Volume Pricing	1 In Stock
685.00	50	#26-949	S\$1,288.00 Volume Pricing	1 In Stock
785.00	10	#26-950	S\$742.00 Volume Pricing	1 In Stock
785.00	20	#26-951	S\$833.00 Volume Pricing	2 In Stock
785.00	50	#26-952	S\$924.00 Volume Pricing	1 In Stock
830.00	10	#26-953	S\$833.00 Volume Pricing	1 In Stock
830.00	20	#26-954	S\$924.00 Volume Pricing	1 In Stock
830.00	50	#26-955	S\$1,015.00 Volume Pricing	2 In Stock
850.00	10	#26-956	S\$742.00 Volume Pricing	3 In Stock
850.00	20	#26-957	S\$833.00 Volume Pricing	2 In Stock
850.00	50	#26-958	S\$924.00 Volume Pricing	1 In Stock
940.00	10	#26-959	S\$875.00 Volume Pricing	4 In Stock
940.00	20	#26-960	S\$966.00 Volume Pricing	5 In Stock
940.00	50	#26-961	S\$1,064.00 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com