

[All Products](#) / [Lights and Illumination](#) / [Spectroscopy Lighting](#)

Digital Fiber Coupled LEDs



- Wavelengths from 275 - 940nm, with Broadband and White LED Options
- High Output Powers up to 250mW
- Integrated Driver and Controller for Ease of Use

Common Specifications

General

Operating Lifetime (hours): ~10,000

Contents of Kit:

- 1 x Fiber-coupled LED Unit
- 1 x 12V DC Power Supply
- 1 x International AC Socket Clip
- 1 x USB to RS232 adapter cable

Note: Fiberoptic Patch Cords sold separately

Hardware & Interface Connectivity

Connector: SMA

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Connector	Stock Number	Price	Buy
275	3	SMA	#70-896	S\$2,093.00 Volume Pricing	1 In Stock
280	3	SMA	#70-897	S\$2,093.00 Volume Pricing	1 In Stock
365	290	SMA	#70-898	S\$1,799.00 Volume Pricing	3 In Stock
395	350	SMA	#70-899	S\$1,799.00 Volume Pricing	1 In Stock
405	360	SMA	#70-900	S\$1,799.00 Volume Pricing	1 In Stock
455	320	SMA	#70-901	S\$1,799.00 Volume Pricing	1 In Stock
475	210	SMA	#70-902	S\$1,799.00 Volume Pricing	1 In Stock
490	140	SMA	#70-903	S\$1,953.00 Volume Pricing	1 In Stock
530	100	SMA	#70-904	S\$1,799.00 Volume Pricing	1 In Stock
550	200	SMA	#70-905	S\$1,799.00 Volume Pricing	3 In Stock
595	100	SMA	#70-906	S\$1,799.00 Volume Pricing	1 In Stock
630	130	SMA	#70-907	S\$1,799.00 Volume Pricing	3 In Stock
680	130	SMA	#70-908	S\$1,953.00 Volume Pricing	1 In Stock
750	90	SMA	#70-909	S\$1,953.00 Volume Pricing	1 In Stock
810	140	SMA	#70-910	S\$1,953.00 Volume Pricing	1 In Stock
850	130	SMA	#70-911	S\$1,953.00 Volume Pricing	1 In Stock
940	120	SMA	#70-912	S\$1,953.00 Volume Pricing	1 In Stock

-	20	SMA	#70-913	S\$2,093.00 Volume Pricing	1 In Stock
-	220	SMA	#70-914	S\$1,953.00 Volume Pricing	1 In Stock
-	140	SMA	#70-915	S\$1,953.00 Volume Pricing	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com