

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Bandpass Filters](#)

High Transmission Traditional Coated Bandpass Filters



- Passband Transmission up to 80%
- 441.6 to 1064nm Wavelength Options with 10, 20, and 40nm Bandwidths
- Ideal for Medical and Analytical Applications

Common Specifications

Physical & Mechanical Properties

Construction:

Mounted in Black Anodized Ring

Optical Properties

Coating:

Traditional Coated

Environmental & Durability Factors

Operating Temperature (°C):

-50 to +70

Technical Information

Products

CWL (nm)	Dia. (mm)	FWHM (nm)	Stock Number	Price	Buy
441.60	12.50	10.00	#71-604	S\$161.00 Volume Pricing	3 In Stock
441.60	25.00	10.00	#71-605	S\$315.00 Volume Pricing	3 In Stock
441.60	50.00	10.00	#71-606	S\$770.00 Volume Pricing	1 In Stock
450.00	12.50	10.00	#71-607	S\$161.00 Volume Pricing	3 In Stock
450.00	25.00	10.00	#71-608	S\$315.00 Volume Pricing	1 In Stock
450.00	50.00	10.00	#71-609	S\$770.00 Volume Pricing	1 In Stock
450.00	12.50	20.00	#71-610	S\$161.00 Volume Pricing	3 In Stock
450.00	25.00	20.00	#71-611	S\$315.00 Volume Pricing	3 In Stock
450.00	50.00	20.00	#71-612	S\$770.00 Volume Pricing	1 In Stock
450.00	12.50	40.00	#71-613	S\$161.00 Volume Pricing	2 In Stock
450.00	25.00	40.00	#71-614	S\$315.00 Volume Pricing	2 In Stock
450.00	50.00	40.00	#71-615	S\$770.00 Volume Pricing	1 In Stock
457.90	12.50	10.00	#71-616	S\$161.00 Volume Pricing	3 In Stock
457.90	25.00	10.00	#71-617	S\$315.00 Volume Pricing	3 In Stock
457.90	50.00	10.00	#71-618	S\$770.00 Volume Pricing	1 In Stock
486.10	12.50	10.00	#71-619	S\$161.00 Volume Pricing	3 In Stock
486.10	25.00	10.00	#71-620	S\$315.00 Volume Pricing	3 In Stock
486.10	50.00	10.00	#71-621	S\$770.00 Volume Pricing	2 In Stock

488.00	12.50	10.00	#71-622	S\$161.00 Volume Pricing	3 In Stock
488.00	25.00	10.00	#71-623	S\$315.00 Volume Pricing	1 In Stock
488.00	50.00	10.00	#71-624	S\$770.00 Volume Pricing	1 In Stock
500.00	12.50	10.00	#71-625	S\$161.00 Volume Pricing	3 In Stock
500.00	25.00	10.00	#71-626	S\$315.00 Volume Pricing	3 In Stock
500.00	50.00	10.00	#71-627	S\$770.00 Volume Pricing	1 In Stock
500.00	12.50	20.00	#71-628	S\$161.00 Volume Pricing	3 In Stock
500.00	25.00	20.00	#71-629	S\$315.00 Volume Pricing	3 In Stock
500.00	50.00	20.00	#71-630	S\$770.00 Volume Pricing	1 In Stock
500.00	12.50	40.00	#71-631	S\$161.00 Volume Pricing	3 In Stock
500.00	25.00	40.00	#71-632	S\$315.00 Volume Pricing	3 In Stock
500.00	50.00	40.00	#71-633	S\$770.00 Volume Pricing	1 In Stock
514.50	12.50	10.00	#71-634	S\$161.00 Volume Pricing	3 In Stock
514.50	25.00	10.00	#71-635	S\$315.00 Volume Pricing	3 In Stock
514.50	50.00	10.00	#71-636	S\$770.00 Volume Pricing	1 In Stock
532.00	12.50	10.00	#71-637	S\$161.00 Volume Pricing	3 In Stock
532.00	25.00	10.00	#71-638	S\$315.00 Volume Pricing	3 In Stock
532.00	50.00	10.00	#71-639	S\$770.00 Volume Pricing	1 In Stock
546.10	12.50	10.00	#71-640	S\$161.00 Volume Pricing	3 In Stock
546.10	25.00	10.00	#71-641	S\$315.00 Volume Pricing	3 In Stock

546.10	50.00	10.00	#71-642	S\$770.00 Volume Pricing	1 In Stock
550.00	12.50	10.00	#71-643	S\$161.00 Volume Pricing	3 In Stock
550.00	25.00	10.00	#71-644	S\$315.00 Volume Pricing	3 In Stock
550.00	50.00	10.00	#71-645	S\$770.00 Volume Pricing	1 In Stock
550.00	12.50	20.00	#71-646	S\$161.00 Volume Pricing	3 In Stock
550.00	25.00	20.00	#71-647	S\$315.00 Volume Pricing	3 In Stock
550.00	50.00	20.00	#71-648	S\$770.00 Volume Pricing	1 In Stock
550.00	12.50	40.00	#71-649	S\$161.00 Volume Pricing	1 In Stock
550.00	25.00	40.00	#71-650	S\$315.00 Volume Pricing	2 In Stock
550.00	50.00	40.00	#71-651	S\$770.00 Volume Pricing	1 In Stock
577.00	12.50	10.00	#71-652	S\$161.00 Volume Pricing	3 In Stock
570.00	25.00	10.00	#71-653	S\$315.00 Volume Pricing	2 In Stock
570.00	50.00	10.00	#71-654	S\$770.00 Volume Pricing	1 In Stock
589.30	12.50	10.00	#71-655	S\$161.00 Volume Pricing	3 In Stock
589.30	25.00	10.00	#71-656	S\$315.00 Volume Pricing	3 In Stock
589.30	50.00	10.00	#71-657	S\$770.00 Volume Pricing	1 In Stock
600.00	12.50	10.00	#71-658	S\$161.00 Volume Pricing	3 In Stock
600.00	25.00	10.00	#71-659	S\$315.00 Volume Pricing	3 In Stock
600.00	50.00	10.00	#71-660	S\$770.00 Volume Pricing	1 In Stock
600.00	12.50	20.00	#71-661	S\$161.00 Volume Pricing	3 In Stock

600.00	25.00	20.00	#71-662	S\$315.00 Volume Pricing	3 In Stock
600.00	50.00	20.00	#71-663	S\$770.00 Volume Pricing	1 In Stock
600.00	12.50	40.00	#71-664	S\$161.00 Volume Pricing	2 In Stock
600.00	25.00	40.00	#71-665	S\$315.00 Volume Pricing	3 In Stock
600.00	50.00	40.00	#71-666	S\$770.00 Volume Pricing	1 In Stock
632.80	12.50	10.00	#71-667	S\$161.00 Volume Pricing	3 In Stock
632.80	25.00	10.00	#71-668	S\$315.00 Volume Pricing	2 In Stock
632.80	50.00	10.00	#71-669	S\$770.00 Volume Pricing	1 In Stock
636.20	12.50	10.00	#71-670	S\$161.00 Volume Pricing	3 In Stock
636.20	25.00	10.00	#71-671	S\$315.00 Volume Pricing	3 In Stock
636.20	50.00	10.00	#71-672	S\$770.00 Volume Pricing	1 In Stock
650.00	12.50	10.00	#71-673	S\$161.00 Volume Pricing	2 In Stock
650.00	25.00	10.00	#71-674	S\$315.00 Volume Pricing	2 In Stock
650.00	50.00	10.00	#71-675	S\$770.00 Volume Pricing	1 In Stock
650.00	12.50	20.00	#71-676	S\$161.00 Volume Pricing	3 In Stock
650.00	25.00	20.00	#71-677	S\$315.00 Volume Pricing	3 In Stock
650.00	50.00	20.00	#71-678	S\$770.00 Volume Pricing	1 In Stock
650.00	12.50	40.00	#71-679	S\$161.00 Volume Pricing	1 In Stock
650.00	25.00	40.00	#71-680	S\$315.00 Volume Pricing	3 In Stock
650.00	50.00	40.00	#71-681	S\$770.00 Volume Pricing	1 In Stock

656.30	12.50	10.00	#71-682	S\$161.00 Volume Pricing	1 In Stock
656.30	25.00	10.00	#71-683	S\$315.00 Volume Pricing	3 In Stock
656.30	50.00	10.00	#71-684	S\$770.00 Volume Pricing	1 In Stock
660.00	12.50	10.00	#71-685	S\$161.00 Volume Pricing	3 In Stock
660.00	25.00	10.00	#71-686	S\$315.00 Volume Pricing	3 In Stock
660.00	50.00	10.00	#71-687	S\$770.00 Volume Pricing	1 In Stock
670.80	12.50	10.00	#71-688	S\$161.00 Volume Pricing	3 In Stock
670.80	25.00	10.00	#71-689	S\$315.00 Volume Pricing	3 In Stock
670.80	50.00	10.00	#71-690	S\$770.00 Volume Pricing	1 In Stock
694.30	12.50	10.00	#71-691	S\$161.00 Volume Pricing	3 In Stock
694.30	25.00	10.00	#71-692	S\$315.00 Volume Pricing	3 In Stock
694.30	50.00	10.00	#71-693	S\$770.00 Volume Pricing	1 In Stock
700.00	12.50	10.00	#71-694	S\$161.00 Volume Pricing	3 In Stock
700.00	25.00	10.00	#71-696	S\$315.00 Volume Pricing	2 In Stock
700.00	50.00	10.00	#71-697	S\$770.00 Volume Pricing	1 In Stock
700.00	12.50	20.00	#71-698	S\$161.00 Volume Pricing	3 In Stock
700.00	25.00	20.00	#71-699	S\$315.00 Volume Pricing	3 In Stock
700.00	50.00	20.00	#71-700	S\$770.00 Volume Pricing	1 In Stock
700.00	12.50	40.00	#71-701	S\$161.00 Volume Pricing	3 In Stock
700.00	25.00	40.00	#71-702	S\$315.00 Volume Pricing	3 In Stock

700.00	50.00	40.00	#71-703	S\$770.00 Volume Pricing	Contact Us
750.00	12.50	10.00	#71-704	S\$161.00 Volume Pricing	1 In Stock
750.00	25.00	10.00	#71-705	S\$315.00 Volume Pricing	3 In Stock
750.00	50.00	10.00	#71-706	S\$770.00 Volume Pricing	1 In Stock
750.00	12.50	20.00	#71-707	S\$161.00 Volume Pricing	3 In Stock
750.00	25.00	20.00	#71-708	S\$315.00 Volume Pricing	2 In Stock
750.00	50.00	20.00	#71-709	S\$770.00 Volume Pricing	1 In Stock
750.00	12.50	40.00	#71-711	S\$161.00 Volume Pricing	3 In Stock
750.00	25.00	40.00	#71-712	S\$315.00 Volume Pricing	3 In Stock
750.00	50.00	40.00	#71-713	S\$770.00 Volume Pricing	1 In Stock
766.50	12.50	10.00	#71-714	S\$161.00 Volume Pricing	3 In Stock
766.50	25.00	10.00	#71-715	S\$315.00 Volume Pricing	3 In Stock
766.50	50.00	10.00	#71-716	S\$770.00 Volume Pricing	1 In Stock
780.00	12.50	10.00	#71-717	S\$161.00 Volume Pricing	3 In Stock
780.00	25.00	10.00	#71-718	S\$315.00 Volume Pricing	3 In Stock
780.00	50.00	10.00	#71-719	S\$770.00 Volume Pricing	1 In Stock
794.70	12.50	10.00	#71-720	S\$161.00 Volume Pricing	3 In Stock
794.70	25.00	10.00	#71-721	S\$315.00 Volume Pricing	2 In Stock
794.70	50.00	10.00	#71-722	S\$770.00 Volume Pricing	1 In Stock
800.00	12.50	10.00	#71-723	S\$161.00 Volume Pricing	3 In Stock

800.00	25.00	10.00	#71-724	S\$315.00 Volume Pricing	3 In Stock
800.00	50.00	10.00	#71-725	S\$770.00 Volume Pricing	1 In Stock
800.00	12.50	20.00	#71-726	S\$161.00 Volume Pricing	3 In Stock
800.00	25.00	20.00	#71-727	S\$315.00 Volume Pricing	1 In Stock
800.00	50.00	20.00	#71-728	S\$770.00 Volume Pricing	1 In Stock
800.00	12.50	40.00	#71-729	S\$161.00 Volume Pricing	3 In Stock
800.00	25.00	40.00	#71-730	S\$315.00 Volume Pricing	2 In Stock
800.00	50.00	40.00	#71-731	S\$770.00 Volume Pricing	2 In Stock
810.00	12.50	10.00	#71-732	S\$161.00 Volume Pricing	2 In Stock
810.00	25.00	10.00	#71-733	S\$315.00 Volume Pricing	3 In Stock
810.00	50.00	10.00	#71-734	S\$770.00 Volume Pricing	2 In Stock
810.00	12.50	20.00	#71-735	S\$161.00 Volume Pricing	1 In Stock
810.00	25.00	20.00	#71-736	S\$315.00 Volume Pricing	1 In Stock
810.00	50.00	20.00	#71-737	S\$770.00 Volume Pricing	1 In Stock
830.00	12.50	10.00	#71-738	S\$161.00 Volume Pricing	2 In Stock
830.00	25.00	10.00	#71-739	S\$315.00 Volume Pricing	3 In Stock
830.00	50.00	10.00	#71-740	S\$770.00 Volume Pricing	1 In Stock
830.00	12.50	20.00	#71-741	S\$161.00 Volume Pricing	3 In Stock
830.00	25.00	20.00	#71-742	S\$315.00 Volume Pricing	3 In Stock
830.00	50.00	20.00	#71-743	S\$770.00 Volume Pricing	1 In Stock

850.00	12.50	10.00	#71-744	S\$161.00 Volume Pricing	3 In Stock
850.00	25.00	10.00	#71-745	S\$315.00 Volume Pricing	3 In Stock
850.00	50.00	10.00	#71-746	S\$770.00 Volume Pricing	1 In Stock
850.00	12.50	20.00	#71-747	S\$161.00 Volume Pricing	2 In Stock
850.00	25.00	20.00	#71-748	S\$315.00 Volume Pricing	1 In Stock
850.00	50.00	20.00	#71-749	S\$770.00 Volume Pricing	1 In Stock
850.00	12.50	40.00	#71-750	S\$161.00 Volume Pricing	3 In Stock
850.00	25.00	40.00	#71-751	S\$315.00 Volume Pricing	2 In Stock
850.00	50.00	40.00	#71-752	S\$770.00 Volume Pricing	1 In Stock
900.00	12.50	10.00	#71-753	S\$161.00 Volume Pricing	3 In Stock
900.00	25.00	10.00	#71-754	S\$315.00 Volume Pricing	3 In Stock
900.00	50.00	10.00	#71-755	S\$770.00 Volume Pricing	1 In Stock
900.00	12.50	20.00	#71-756	S\$161.00 Volume Pricing	3 In Stock
900.00	25.00	20.00	#71-757	S\$315.00 Volume Pricing	3 In Stock
900.00	50.00	20.00	#71-758	S\$770.00 Volume Pricing	1 In Stock
900.00	12.50	40.00	#71-759	S\$161.00 Volume Pricing	1 In Stock
900.00	25.00	40.00	#71-760	S\$315.00 Volume Pricing	3 In Stock
900.00	50.00	40.00	#71-761	S\$770.00 Volume Pricing	1 In Stock
905.00	12.50	10.00	#71-762	S\$161.00 Volume Pricing	3 In Stock
905.00	25.00	10.00	#71-763	S\$315.00 Volume Pricing	2 In Stock

905.00	50.00	10.00	#71-764	S\$770.00 Volume Pricing	1 In Stock
950.00	12.50	10.00	#71-765	S\$161.00 Volume Pricing	3 In Stock
950.00	25.00	10.00	#71-766	S\$315.00 Volume Pricing	3 In Stock
950.00	50.00	10.00	#71-767	S\$770.00 Volume Pricing	1 In Stock
950.00	12.50	40.00	#71-768	S\$161.00 Volume Pricing	2 In Stock
950.00	25.00	40.00	#71-769	S\$315.00 Volume Pricing	3 In Stock
950.00	50.00	40.00	#71-770	S\$770.00 Volume Pricing	1 In Stock
1,064.00	12.50	10.00	#71-771	S\$161.00 Volume Pricing	3 In Stock
1,064.00	25.00	10.00	#71-772	S\$315.00 Volume Pricing	1 In Stock
1,064.00	50.00	10.00	#71-773	S\$770.00 Volume Pricing	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com