



FOCAL LENGTH (EFL):  $15 \pm 0,15$   
 BACK FOCAL LENGTH (BFL): 13,8

1 AR COATING: VIS-EXT  
 $R(\text{AVG}) \leq 0,5\%$  FROM 350-700nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	14,88±0,015 CX	GLASS N-BK7 517/642	R	14,88±0,015 CX
Øe	9		Øe	9
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

10mm Dia, x 15mm FL, VIS-EXT Coated, Double-Convex Lens

DWG NO

89143

SHEET SIZE  
A4

SHEET  
1 OF 1