




NOTES:

1. SUBSTRATE: Fused Silica (Corning 7980)
2. RoHS COMPLIANT
3. SURFACE S2 TO BE PARALLEL WITH SURFACE S 1 TO WITHIN ACRMIN
4. Coating (Apply Across Clear Aperture):
S1 & S2: Ravg $\leq 1.75\%$ @ 400 - 700nm



5. FINE GROUND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 |
|------------------|---------------------|---------------------|
| Shape | Plano | Plano |
| Surface Accuracy | 1λ | 1λ |
| Surface Quality | 60-40 | 60-40 |
| Clear Aperture | 22.86 | 22.86 |
| Bevel | Protected as Needed | Protected as Needed |

THIRD ANGLE
PROJECTION



Edmund Optics®

25.4mm Dia. 2mm Thick MgF₂ Coated, 1λ
Fused Silica Window

ALL DIMS IN

mm

DWG NO

25320

SHEET
77 OF 101