

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Focusing \(Concave\) Mirrors](#)

TECHSPEC® $\lambda/8$ Precision Spherical Mirrors



- Ideal for Multispectral Focusing Applications
- Variety of Coating Options Offered
- Multiple Sizes Available
- [\$\lambda/4\$ Spherical Mirrors](#) Also Available

Common Specifications


Physical & Mechanical Properties

Back Surface:	Ground	Edge Thickness Tolerance (%):	+0.0/-10
---------------	--------	-------------------------------	----------

Optical Properties

Substrate:	BOROFLOAT®	Surface Quality:	60-40
Surface Accuracy:	$\lambda/8$		

Technical Information



Products

Surface Accuracy	Dia. (mm)	EFL (mm)	Aperture (f/#)	Coating	Stock Number	Price	Buy
λ/8	107.95	1,143.00	f/10.6	Protected Aluminum (400-2000nm)	#50-051	S\$888.63 Volume Pricing	1 In Stock
λ/8	152.40	1,524.00	f/10	Protected Aluminum (400-2000nm)	#71-026	S\$1,082.79 Volume Pricing	9 In Stock
#32-081 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
λ/8	63.50	635.00	f/10	Uncoated		S\$232.91	7 In Stock

[#32-082 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

λ/8

76.20

762.00

f/10

Uncoated

S\$283.69

5 In Stock

[#32-083 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

λ/8

108.00

1,143.00

f/10.6

Uncoated

S\$634.74

Contact Us

[#32-084 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

λ/8	152.40	1,524.00	f/10	Uncoated	S\$799.02	1 In Stock
-----	--------	----------	------	----------	-----------	------------

