


[All Products](#) /
 [Optics](#) /
 [Diffraction Gratings](#) /
 [Transmissive Diffraction Gratings](#)

Transmission Grating Beamsplitters



- Ideal for Laser Beam Division
- Designed for 0 Degree AOI
- Low Groove Density for Maximized Beam Separation

Common Specifications


Physical & Mechanical Properties

Clear Aperture (%):	90	Construction:	Blazed Grating
Thickness (mm):	3.00 ±0.5		

Optical Properties

Design Wavelength DWL (nm):	632.8
Substrate:	B270

Technical Information



Products

Groove Density (grooves/mm)	DWL (nm)	Dimensions (mm)	Stock Number	Price	Buy
70	632.8	12.7 x 12.7	#46-067	S\$217.00 Volume Pricing	13 In Stock
80	632.8	12.7 x 12.7	#46-069	S\$210.00 Volume Pricing	11 In Stock
92	632.8	12.7 x 12.7	#46-071	S\$210.00 Volume Pricing	5 In Stock
110	632.8	12.7 x 12.7	#46-073	S\$210.00 Volume Pricing	5 In Stock
70	632.8	25.0 x 25.0	#46-068	S\$441.00 Volume Pricing	7 In Stock
80	632.8	25.0 x 25.0	#46-070	S\$441.00 Volume Pricing	5 In Stock
92	632.8	25.0 x 25.0	#46-072	S\$441.00 Volume Pricing	4 In Stock
110	632.8	25.0 x 25.0	#46-074	S\$441.00 Volume Pricing	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com