

[All Products](#) / [Lasers](#) / [Laser Measurement and Electronics](#) / [Laser Power Meters](#)

Premier Laser Diode Detector



- Designed for Use with the [Premier Laser Diodes](#)
- Wide Acceptance Angle
- Ideal for Particle Detection and Densitometry

Common Specifications

Physical & Mechanical Properties			
Diameter (mm):	15.00	Length (mm):	54.50
Weight (g):	50.00	Construction:	Anodized Aluminum
Electrical			
AC & DC S/N Ratio for 1mW Input (dB):	>60	Current (mA):	<20
Voltage (V):	5 - 10 DC		
Hardware & Interface Connectivity			
Connector:	4 pin JST		
Power Supply:	Power Supply Required and Sold Separately: USA: #59-099 Europe: Not Available Japan: #59-099 Korea: Not Available China: #59-099	Electrical Leads/ Pin Connections:	4 input/output leads
Environmental & Durability Factors			
Operating Humidity:	90% RH	Storage Temperature (°C):	-40 to +85

Technical Information

Products

Title	Stock Number	Price	Buy
Standard, Premier Laser Diode Detector	#58-760	S\$175.00 Volume Pricing	2 In Stock
High Gain, Premier Laser Diode Detector	#58-764	S\$182.00 Volume Pricing	2 In Stock
High Frequency, Premier Laser Diode Detector	#58-765	S\$182.00 Volume Pricing	3 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com