

[All Products](#) / [Optics](#) / [Prisms](#) / [Dispersion Prisms](#)
TECHSPEC® 30° - 60° - 90° Littrow Dispersion Prisms



- Ray Deviation of 60° If Coated
- Ideal as a Dispersion Prism if Uncoated
- Right Handed Image

Common Specifications


Physical & Mechanical Properties

Dimensional Tolerance (mm): ±0.13	Bevel: Protective as needed
Optical Properties	
Substrate: N-BK7	Surface Quality: 80-50
Angle Tolerance (arcmin): ±10	Image Orientation: Right-Handed
Ray Deviation (°): 60	Power (fringes) @ 632.8nm: 3.00
Irregularity (fringes) @ 632.8nm: 1.00	

Technical Information



Littrow Dispersion Prism Ray Path



Littrow Dispersion Prism Tunnel Diagram

Products

Length (mm)	Coating	Substrate	Stock Number	Price	Buy
12.70	Protected Aluminum (400-2000nm)	N-BK7	#43-672	S\$120.22 Volume Pricing	20+ In Stock
12.70	Uncoated	N-BK7	#43-648	S\$97.08 Volume Pricing	20+ In Stock
22.00	Protected Aluminum (400-2000nm)	N-BK7	#43-673	S\$132.17 Volume Pricing	20+ In Stock
22.00	Uncoated	N-BK7	#43-649	S\$109.03 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com