

[All Products](#) / [Lasers](#) / [Laser Measurement and Electronics](#) / [Laser Power Meters](#)

Coherent® Laser Power and Energy Meters

[See More by Coherent®](#)

- Coherent® [Thermopile Power Sensors](#), [Position Sensing Thermopile Sensors](#), [Laser Energy Sensors](#), or [High Sensitivity Sensors](#) Sold Separately
- FieldMate Used to Measure Laser Power
- FieldMaxII Used to Measure Laser Power and Energy
- ISO 17025 Certified

Common Specifications

General

Calibration Uncertainty (%): ±1.0

Environmental & Durability Factors

Operating Temperature (°C): +5 to +40

Storage Temperature (°C): -20 to +70

Technical Information

Products

Type	Resolution	Power Sampling Rate (Hz)	Computer Interface	Model Number	Stock Number	Price	Buy
Power, Energy, and Beam Position	0.1% Full Scale at 10Hz, 0.2% Full Scale at 20kHz	625,000	USB & RS232	1268881	#35-203	\$2,359.00	Contact Us

[#35-203-RCD-05P Recertified](#)



Recertified

Stock No.: 35-203-RCD-05P
Recertified Code: 05P (All Original Parts Included, Perfect)

Recertified Products

Typically 1-2 Recertified Products are in stock at a time. Please contact our sales team if you would like exact availability of an item.

Recertified products are those identified with the recertified logo indicating they were returned to Edmund Optics® and cannot be sold as new for the following reasons:

- Open Box – Missing original packaging
- Cosmetic Blemishes – Scratches, rub marks or other minor cosmetic imperfections
- Service/Repair – Product has been serviced to the factory original specification
- Factory Returns – Product has been returned in its original condition

Power, Energy, and Beam Position	0.1% Full Scale at 10Hz, 0.2% Full Scale at 20kHz	625,000	USB & RS232	1268881	\$1,813.00	3 In Stock
----------------------------------	---	---------	-------------	---------	------------	------------

Recertified products are inspected for damage and any necessary repairs are made. Products are then certified by Edmund Optics® to be in good working order. Since quantity is low, recertified products are sold on a first come, first serve basis. Any imperfections will be listed in the description, indicated in the stock number, and categorized by the table below. When purchasing recertified products, the Edmund Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the Web Specials section of our website.

[Parts](#) [Cosmetic](#)

05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		

Power Only	0.1% of Full Scale (10s Scale)	20	-	1098297	#59-978	\$1,610.00	2 In Stock
Power Only	0.1% Full Scale	10	USB	1098579	#88-411	\$1,855.00	5 In Stock
Power and Energy	0.1% Full Scale	10	USB	1098580	#66-277	\$2,569.00	5 In Stock

[#66-277-RCD-05P Recertified](#)



Recertified

Stock No.: 66-277-RCD-05P
Recertified Code: 05P (All Original Parts Included, Perfect)

Recertified Products

Typically 1-2 Recertified Products are in stock at a time. Please contact our sales team if you would like exact availability of an item.

Recertified products are those identified with the recertified logo indicating they were returned to Edmund Optics® and cannot be sold as new for the following reasons:

- Open Box – Missing original packaging
- Cosmetic Blemishes – Scratches, rub marks or other minor cosmetic imperfections
- Service/Repair – Product has been serviced to the factory original specification
- Factory Returns – Product has been returned in its original condition

Recertified products are inspected for damage and any necessary repairs are made. Products are then certified by Edmund Optics® to be in good working order. Since quantity is low, recertified

Power and Energy	0.1% Full Scale	10	USB	1098580	\$2,046.00	1 In Stock
------------------	-----------------	----	-----	---------	------------	------------

products are sold on a first come, first serve basis. Any imperfections will be listed in the description, indicated in the stock number, and categorized by the table below. When purchasing recertified products, the Edmund Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the Web Specials section of our website.

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		

Power and Energy	±0.04% (25% to full scale), ±0.26% (5% to 25% of full scale), ±1% (min to 5% of full scale)	10	Ethernet, USB, RS-232, PC application	2256258	#23-660	S\$3,171.00	3 In Stock
Power and Energy	±0.04% (25% to full scale), ±0.26% (5% to 25% of full scale), ±1% (min to 5% of full scale)	10	Ethernet, USB, RS-232, PC application	2256259	#23-661	S\$3,549.00	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com