

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Polished](#)

TECHSPEC® Hyperbolic Aspheric Lenses



- Designed and Coated for Nd:YAG Laser Wavelengths
- Aspheric Figure Error of 1.6λ RMS and 6λ PV
- Modified [TECHSPEC® PCX Lenses](#)

Common Specifications


Physical & Mechanical Properties

Diameter (mm):	25.00 +0.0/-0.1	Centering (arcmin):	≤ 5
Clear Aperture CA (mm):	23.00	Bevel:	Protective as needed
Shape of Back Surface:	Convex		

Optical Properties

Substrate:	N-BK7		
Surface Quality:	40-20	Conjugate Distance:	Infinite
Asphere Figure Error, @ 632.8nm:	1.6λ RMS and 6λ PV		

Technical Information



Products

Dia. (mm)	EFL (mm)	NA	Coating	Stock Number	Price	Buy
25.00	25.00	0.50	Laser V-Coat (532nm)	#89-431	S\$382.20 Volume Pricing	6 In Stock
25.00	25.00	0.50	Laser V-Coat (1064nm)	#89-439	S\$382.20 Volume Pricing	9 In Stock
25.00	50.00	0.25	Laser V-Coat (532nm)	#89-432	S\$382.20 Volume Pricing	20+ In Stock
25.00	50.00	0.25	Laser V-Coat (1064nm)	#89-440	S\$382.20 Volume Pricing	1 In Stock
25.00	75.00	0.17	Laser V-Coat (532nm)	#89-433	S\$382.20 Volume Pricing	3 In Stock
25.00	75.00	0.17	Laser V-Coat (1064nm)	#89-441	S\$382.20 Volume Pricing	5 In Stock
25.00	100.00	0.13	Laser V-Coat (532nm)	#89-434	S\$382.20 Volume Pricing	13 In Stock
25.00	100.00	0.13	Laser V-Coat (1064nm)	#89-442	S\$382.20 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com