

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Achromatic Lenses](#)

TECHSPEC® C-Mount Achromatic Pairs



- C-Mount Designs for Easy Integration into Imaging Applications
- Feature Integrated Iris for Increased Control of Light Throughput
- Ideal for Relay or Projection Applications

Common Specifications


Physical & Mechanical Properties

Aperture (mm):	0.8 - 20	Housing Diameter (mm):	38.00
Housing Length (mm):	45.9		

Optical Properties

Surface Quality:	40-20		
Coating:	VIS 0° (425-675nm)	Coating Specification:	$R_{avg} \leq 0.4\% @ 425 - 675nm$
Wavelength Range (nm):	425 - 675		

Technical Information



Products

Coating	EFL A (mm)	EFL B (mm)	Housing Diameter (mm)	Magnification	Object Distance (mm)	Stock Number	Price	Buy
VIS 0° (425-675nm)	30.0	30.0	38.00	1:1	15.00	#87-185	S\$575.00 Volume Pricing	1 In Stock
VIS 0° (425-675nm)	30.0	60.0	38.00	1:2	15.00	#87-186	S\$575.00 Volume Pricing	Contact Us
VIS 0° (425-675nm)	30.0	100.0	38.00	1:3.33	15.00	#87-187	S\$575.00 Volume Pricing	16 In Stock
VIS 0° (425-675nm)	50.0	50.0	38.00	1:1	35.00	#87-188	S\$575.00 Volume Pricing	Contact Us
VIS 0° (425-675nm)	50.0	100.0	38.00	1:2	35.00	#87-189	S\$575.00 Volume Pricing	Contact Us
VIS 0° (425-675nm)	75.0	75.0	38.00	1:1	60.00	#87-190	S\$575.00 Volume Pricing	Contact Us
VIS 0° (425-675nm)	75.0	150.0	38.00	1:2	60.00	#87-191	S\$575.00 Volume Pricing	Contact Us
VIS 0° (425-675nm)	100.0	100.0	38.00	1:1	85.00	#87-192	S\$575.00 Volume Pricing	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com