


[All Products](#) /
 [Optics](#) /
 [Optical Lenses](#) /
 [Cylinder Lenses](#) /
 [Specialty Lenses](#)

Fast Axis Collimators



- Aspheric Cylindrical Lens Designs for Fast Axis Collimation
- Standard AR Coating for 790 – 990nm
- Ideal for Laser Diode Collimation
- [Slow Axis Collimators](#) Also Available

Common Specifications

Physical & Mechanical Properties

Height Tolerance (mm):	±0.05	Length (mm):	12.00
Length Tolerance (mm):	±0.05	Width Tolerance (mm):	±0.01

Optical Properties

Substrate:	S-TiH53	Coating:	BBAR (790-990nm)
Wavelength Range (nm):	790 - 990	Coating Specification:	$R_{avg} < 1.0\%$ @ 790 - 990nm
Surface Accuracy:	$\lambda/4$	Transmission (%):	>99

Technical Information

Products

Length (mm)	EFL (mm)	Substrate	Coating	Stock Number	Price	Buy
12.00	0.29	S-TIH53	BBAR (790-990nm)	#87-349	S\$294.00 Volume Pricing	9 In Stock
12.00	0.36	S-TIH53	BBAR (790-990nm)	#87-350	S\$294.00 Volume Pricing	8 In Stock
12.00	0.59	S-TIH53	BBAR (790-990nm)	#87-351	S\$294.00 Volume Pricing	9 In Stock
12.00	0.91	S-TIH53	BBAR (790-990nm)	#87-352	S\$294.00 Volume Pricing	6 In Stock
12.00	1.50	S-TIH53	BBAR (790-990nm)	#87-353	S\$294.00 Volume Pricing	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com