

[All Products](#) /
 [Optics](#) /
 [Optical Lenses](#) /
 [Aspheric Lenses](#) /
 [Glass Polished](#)

TECHSPEC® Laser Line Coated Aspheric Lenses



- Designed and Coated for Nd:YAG Laser Wavelengths
- High Laser Damage Thresholds
- Low Coefficient of Thermal Expansion

Common Specifications

Physical & Mechanical Properties

Centering (arcmin):	≤5	Bevel:	Protective as needed
Shape of Back Surface:	Plano		

Optical Properties

Substrate:	Fused Silica (Corning 7980)		
Asphere Figure Error, RMS @ 632.8nm:	1.2λ	Surface Quality:	60-40
Conjugate Distance:	Infinite		

Technical Information

Products

Dia. (mm)	EFL (mm)	NA	Coating	Stock Number	Price	Buy
15.00	12.50	0.60	Laser V-Coat (355nm)	#33-009	S\$779.80 Volume Pricing	9 In Stock
15.00	12.50	0.60	Laser V-Coat (532nm)	#33-013	S\$779.80 Volume Pricing	5 In Stock
15.00	12.50	0.60	Laser V-Coat (1064nm)	#33-017	S\$779.80 Volume Pricing	6 In Stock
15.00	15.00	0.50	Laser V-Coat (355nm)	#33-010	S\$779.80 Volume Pricing	Contact Us
15.00	15.00	0.50	Laser V-Coat (532nm)	#33-014	S\$779.80 Volume Pricing	1 In Stock
15.00	15.00	0.50	Laser V-Coat (1064nm)	#33-018	S\$779.80 Volume Pricing	1 In Stock
25.00	25.00	0.50	Laser V-Coat (355nm)	#33-011	S\$863.80 Volume Pricing	5 In Stock
25.00	25.00	0.50	Laser V-Coat (532nm)	#33-015	S\$863.80 Volume Pricing	7 In Stock
25.00	25.00	0.50	Laser V-Coat (1064nm)	#33-019	S\$863.80 Volume Pricing	11 In Stock
25.00	30.00	0.42	Laser V-Coat (355nm)	#33-012	S\$863.80 Volume Pricing	4 In Stock
25.00	30.00	0.42	Laser V-Coat (532nm)	#33-016	S\$863.80 Volume Pricing	9 In Stock
25.00	30.00	0.42	Laser V-Coat (1064nm)	#33-020	S\$863.80 Volume Pricing	14 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com