

[All Products](#) / [Lasers](#) / [Laser Measurement and Electronics](#) / [Laser Power Meters](#)

Coherent® High-Sensitivity Thermopile Sensors See More by [Coherent®](#)



- Broad Spectral Range with High Sensitivity and High Resolution
- Large Active Area Sensors up to 19mm in Diameter
- Flat Broadband Output with No Saturation above 1mW/cm²

Common Specifications

General				
Linearity (%):		±1	Cooling Method:	Air
Response Time (s):		2	Maximum Incident Energy Density:	50mJ/cm ² (10ns, 1064nm)
Optical Properties				
Calibration Wavelength (nm):			514	
Sensor				
Type of Sensor:		Thermopile		
Electrical				
Maximum Incident Power Density (kW/cm ²):			0.5	

Technical Information

Products

Power Range	Power Resolution	Noise Equivalent Power	Wavelength Range (nm)	Active Area Diameter (mm)	Model Number	Stock Number	Price	Buy
500μW - 2W	50μW	-	300 - 11000	19	PM3 Coherent Part Number: 1098336	#12-403	S\$1,754.50	6 In Stock
100μW - 1W	10μW	-	300 - 11000	10	PS10 Coherent Part Number: 1098350	#12-416	S\$2,668.00	1 In Stock
100μW - 1W	-	3μW	300 - 11000	10	PS10 Coherent Part Number: 1174260	#12-411	S\$3,487.25	Contact Us
100μW - 1W	10μW	-	300 - 11000	19	PS19 Coherent Part Number: 1098413	#12-417	S\$2,762.25	Contact Us
100μW - 1W	-	5μW	300 - 11000	19	PS19 Coherent Part Number: 1174261	#12-412	S\$3,487.25	2 In Stock
100μW - 1W	10μW	-	300 - 2000	19	PS19Q Coherent Part Number: 1098341	#12-418	S\$3,110.25	Contact Us
100μW - 1W	-	3μW	300 - 2100	19	PS19Q Coherent Part Number: 1168343	#68-626	S\$4,019.40	3 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com