

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Off-Axis Mirrors](#)

TECHSPEC® Off-Axis Ellipsoidal Mirrors



- <100Å Surface Roughness for Low Scatter
- Diamond Turned Alignment Surfaces
- Ideal for Finite Conjugate Reflection

Common Specifications

Physical & Mechanical Properties

Surface Roughness (Å):	<100 RMS
------------------------	----------


Optical Properties

Substrate:	Aluminum 6061-T6
------------	------------------

Surface Quality:	60-40
------------------	-------

Coating Type:	Metal
---------------	-------

Technical Information



Products

Magnification	Coating	Dimensions (mm)	Stock Number	Price	Buy
2X	Protected Aluminum (400-2000nm)	25.40 x 25.40	#12-495	S\$442.08 Volume Pricing	5 In Stock
2X	Protected Gold (700-10000nm)	25.40 x 25.40	#12-496	S\$519.74 Volume Pricing	Contact Us
2.5X	Protected Aluminum (400-2000nm)	31.75 x 31.75	#12-497	S\$442.08 Volume Pricing	2 In Stock
2.5X	Protected Gold (700-10000nm)	31.75 x 31.75	#12-498	S\$519.74 Volume Pricing	9 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com