

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

ZEISS EC Epiplan Plan Achromat Infinity Corrected Objectives

See More by [ZEISS](#)



- Ideal for Brightfield, Fluorescence, and Differential Interference Contrast Applications
- Enhanced Contrast
- Excellent Color Correction and Flatness of Field

Common Specifications

General

Compatible Tube Lens
Focal Length (mm):

Focal Length: 164.50mm

Manufacturer:

Zeiss

Physical & Mechanical Properties

Maximum Diameter (mm):

30

Optical Properties

Compatible Cover Glass
Thickness (mm):

N/A

Wavelength Range (nm): 480 - 650

Field Number (mm): 23

Parfocal Length (mm): 45

Immersion Liquid: N/A

Threading & Mounting

Mounting Threads:

M27 x 0.75

Environmental & Durability Factors


Operating Temperature (°C):

+10 to +40

Operating Humidity:

75% at 35°C

Technical Information



Products

Magnification	NA	Field Number (mm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
5X	0.13	23	33.00	422030-9902-000	11.8	#13-822	S\$1,092.00	1 In Stock
10X	0.25	23	16.50	422040-9902-000	11	#13-823	S\$1,204.00	4 In Stock
20X	0.4	23	8.20	422050-9903-000	3.2	#13-824	S\$1,694.00	Contact Us
40X	0.6	23	4.10	422060-9901-000	2.2	#13-825	S\$2,541.00	1 In Stock
50X	0.75	23	3.30	422070-9902-000	1	#13-826	S\$2,352.00	5 In Stock
100X	0.85	23	1.60	422090-9902-000	0.87	#13-827	S\$2,849.00	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com