

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Infrared](#)
TECHSPEC® Calcium Fluoride (CaF₂) Aspheric Lenses


- 266nm or 4μm Design Wavelength Options
- High Transmission from 200nm to 7μm
- Diamond Turned for High Surface Accuracy
- Vacuum UV Grade CaF₂ Substrate

Common Specifications


Physical & Mechanical Properties

Diameter (mm):	25.00 +0.00/-0.10	Centering (arcmin):	<1
Clear Aperture CA (mm):	22.50	Edges:	Diamond Turned

Optical Properties

Substrate:	Calcium Fluoride (CaF ₂) Vacuum UV Grade	Asphere Figure Error, RMS @ 632.8nm:	λ/6
Coating:	Uncoated	Surface Quality:	60-40
Wavelength Range (nm):	200 - 7000		

Technical Information



Products

Dia. (mm)	EFL (mm)	NA	Coating	Aspheric DWL (nm)	Stock Number	Price	Buy
25.00	20.00	0.63	Uncoated	266	#13-462	S\$963.31 Volume Pricing	5 In Stock
25.00	25.00	0.50	Uncoated	266	#13-463	S\$784.09 Volume Pricing	4 In Stock
25.00	50.00	0.25	Uncoated	266	#13-464	S\$784.09 Volume Pricing	2 In Stock
25.00	20.00	0.63	Uncoated	4000	#13-465	S\$963.31 Volume Pricing	3 In Stock
25.00	25.00	0.50	Uncoated	4000	#13-466	S\$784.09 Volume Pricing	Contact Us
25.00	50.00	0.25	Uncoated	4000	#13-467	S\$784.09 Volume Pricing	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com