

[All Products](#) / [Testing and Detection](#) / [Detectors](#)

Segmented InGaAs Photodiodes



- Four Individual Active Area Elements
- High Response Uniformity and Low Crosstalk
- Ideal for Position Detection and Beam Alignment
- [Segmented Silicon Photodiodes](#) and [InGaAs Photodiodes](#) Also Available

Common Specifications

Physical & Mechanical Properties

Element Gap (mm):	0.045
-------------------	-------

Electrical

Responsivity @ 1310nm (AW):	0.85 minimum / 0.9 typical
-----------------------------	----------------------------


Responsivity @ 1550nm (AW):	0.9 minimum / 0.95 typical
-----------------------------	----------------------------

Environmental & Durability Factors

Operating Temperature (°C):	-40 to +75
-----------------------------	------------

Storage Temperature (°C):	-55 to +125
---------------------------	-------------

Technical Information



Products

Size of Active Area (mm)	Connector	Stock Number	Price	Buy
1 Dia.	TO-5	#17-077	S\$421.40 Volume Pricing	2 In Stock
3 Dia.	TO-8	#17-078	S\$861.00 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com