

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Industrial and Pointing Lasers](#)

Fiber-Coupled Laser Modules



- 400µm Core Multimode Fiber with SMA Connector
- 50 and 100mW Output Power Options
- VIS and NIR Wavelengths Available
- [Free Space Alignment Lasers](#) Also Available



Common Specifications

General

Type of Laser:	Diode	Laser Class - CDRH:	Class IIIb
----------------	-------	---------------------	------------

Physical & Mechanical Properties

Length of Fiber (m):	1	Length (mm):	151.00
----------------------	---	--------------	--------

Optical Properties

Spatial Mode:	Fiber-Coupled
---------------	---------------

Hardware & Interface Connectivity

Operating Voltage (V):		5.0		
Output Type:		Fiber-Coupled	Connector:	SMA

Environmental & Durability Factors

Operating Temperature (°C):	+15 to +30
-----------------------------	------------

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Stock Number	Price	Buy
405.00	50	#19-477	S\$1,218.00 Volume Pricing	5 In Stock
405.00	100	#19-478	S\$1,393.00 Volume Pricing	5 In Stock
450.00	50	#19-479	S\$1,218.00 Volume Pricing	1 In Stock
450.00	100	#19-480	S\$1,393.00 Volume Pricing	1 In Stock
532.00	50	#19-481	S\$1,526.00 Volume Pricing	5 In Stock
635.00	50	#19-482	S\$1,155.00 Volume Pricing	3 In Stock
635.00	100	#19-483	S\$1,218.00 Volume Pricing	2 In Stock
808.00	50	#19-484	S\$1,050.00 Volume Pricing	1 In Stock
808.00	100	#19-485	S\$1,218.00 Volume Pricing	2 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com