


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Double-Convex \(DCX\) Lenses](#)

Best Form Spherical Lenses



- Asymmetrical Design for Precise Focusing and Small Spot Size
- Uncoated Fused Silica Substrate with 10-5 Surface Quality
- Ideal for Higher Power Laser Applications

Common Specifications

Physical & Mechanical Properties

Centering (arcmin): <1

Bevel: Protective as needed

Optical Properties

Coating: Uncoated

 Substrate: [Fused Silica](#)

Surface Quality: 10-5

Power (P-V) @ 632.8nm: 1.5λ

Irregularity (P-V) @ 632.8nm: λ/4

 Focal Length
 Specification
 Wavelength (nm): 587.6

Wavelength Range (nm): 200 - 2200

Conjugate Distance: Infinite

Technical Information

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Stock Number	Price	Buy
12.50	20.00	17.80	#22-563	S\$133.00 Volume Pricing	13 In Stock
12.50	25.00	22.79	#22-564	S\$133.00 Volume Pricing	7 In Stock
12.50	40.00	38.65	#22-565	S\$133.00 Volume Pricing	13 In Stock
12.50	50.00	48.81	#22-566	S\$133.00 Volume Pricing	12 In Stock
25.00	40.00	35.06	#22-569	S\$161.00 Volume Pricing	20+ In Stock
25.00	50.00	45.02	#22-570	S\$161.00 Volume Pricing	20+ In Stock
25.00	75.00	72.76	#22-571	S\$161.00 Volume Pricing	Contact Us
25.00	100.00	98.31	#22-572	S\$161.00 Volume Pricing	15 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com