


[All Products](#) / [Laser Optics](#) / [Laser Mirrors](#) / [Laser Line Mirrors](#)
TECHSPEC® 920nm Laser Line Mirrors


- >99.8% Absolute Reflectivity at 920nm
- 99.5% Average Reflectivity in the 905 - 935nm Range
- High Laser Damage Threshold
- Wide Range of Laser Line Mirrors Options Available

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Clear Aperture (%):	90
Parallelism (arcmin):	<3		

Optical Properties

Wavelength Range (nm):	905 - 935		
Substrate:	Fused Silica (Corning 7980)	Coating:	Laser Mirror (905-935nm)
Surface Flatness (P-V):	$\lambda/10$	Surface Quality:	10-5

Technical Information

Products

Title	Stock Number	Price	Buy
920nm Laser Line Mirror, 45° AOI, 12.7mm Dia., 6.35mm Thick	#27-557	S\$203.00 Volume Pricing	3 In Stock
920nm Laser Line Mirror, 45° AOI, 25.4mm Dia., 6.35mm Thick	#27-558	S\$240.80 Volume Pricing	20+ In Stock
920nm Laser Line Mirror, 45° AOI, 50.8mm Dia., 9.53mm Thick	#27-559	S\$431.20 Volume Pricing	5 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com