

[All Products](#) / [Optomechanics](#) / [Motorized Translation Stages](#) / [Motorized Linear Stages](#)

Zaber™ Linear Motor XY Microscope Motorized Stages See

More by [Zaber™](#)



- Ultra-Quiet Linear Motors
- 130 x 100mm or 250 x 100mm Travel Options Available
- 1nm Resolution Linear Encoders provide Excellent Accuracy, Repeatability, and Speed
- Compatible with [µManager](#) Open-Source Microscopy Software

Common Specifications

General				
Encoder:		Yes	Manufacturer:	Zaber Technologies Inc.
Type of Motor:		Moving Magnet Track Linear Motor	Encoder Type:	Linear Analog Encoder
Physical & Mechanical Properties				
Type of Movement:		Linear (X-Y)	Guide System:	Crossed Roller Bearing
Accuracy (μm):		5 (Unidirectional)	Backlash (μm):	0
Height (mm):		40.6	Repeatability (μm):	<0.5
Thrust (N):		35	Encoder Resolution:	1nm
Optical Properties				
Resolution (μm):			0.001	
Electrical				
Maximum Operating Current (mA):			2300	
Hardware & Interface Connectivity				
Type of Drive:		Direct Drive Linear Motor	Power Supply: Power Supply Required and Sold Separately: USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294	
Computer Interface:		RS-232		
Environmental & Durability Factors				
Operating Temperature (°C):			0 to 50	

Technical Information

Products

Stage Size (mm)	Type	Travel (mm)	Encoder	Stock Number	Price	Buy
280.5 x 381.9	Metric	130 in X 100 in Y	Yes	#70-660	S\$15,064.00	2 In Stock
280.5 x 501.9	Metric	250 in X 100 in Y	Yes	#70-661	S\$18,088.00	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com