

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Molded](#)

## Rochester Precision Optics (RPO) Infrared Molded Glass Aspheric Lenses



- Precision Infrared Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Constructed with IG6 Infrared Glass Substrates

### Common Specifications

#### Physical & Mechanical Properties

Bevel:	Protective as needed
--------	----------------------

#### Optical Properties

Substrate:	IG6
------------	-----

Coating:	BBAR (800-1200)	Coating Specification:	$R_{avg} < 1\% @ 800 - 1200, 0 - 30^\circ \text{AOI}$
Surface Quality:	80-60	Wavelength Range (nm):	800 - 1200

## Technical Information

## Products

Dia. (mm)	CT (mm)	EFL (mm)	NA (mm)	CA (mm)	Coating	Stock Number	Price	Buy
<a href="#">#73-677 New</a>								
10.00	6.00	4.00	0.4	5.25	BBAR (800-1200)		New	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!
							S\$189.00	20+ In Stock
<a href="#">#73-679 New</a>								
7.20	4.47	6.50	0.42	3.33	BBAR (800-1200)		New	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!
							S\$189.00	20+ In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)