

Allied Vision Mako G-192C 1/1.8" Color CMOS Camera

See More by [Allied Vision](#)



Allied Vision Mako Power over Ethernet (PoE) Cameras (Front)



Stock **#33-517** 1 In Stock

-

1

+

S\$1,029⁵⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,029.50 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

Type:

Color Camera	
G-192C	Model Number:
Allied Vision	Manufacturer:
Mako	Camera Series:
Color	Spectrum:
Physical & Mechanical Properties	
42.6 x 29.2 x 29.2 (excludes connectors and lens mount)	Dimensions (mm):
80	Weight (g):
Full	Housing:
Sensor	
64MB	Image Buffer:
1/1.8"	Sensor Format:
1.90	Resolution (Megapixels):
60.00	Frame Rate (fps):
1,600 x 1,200	Pixels (H x V):
4.5 x 4.5	Pixel Size, H x V (µm):
7.2 x 5.4	Sensing Area, H x V (mm):
e2v EV76C570	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/12 bit	Pixel Depth:
Via Software	Exposure Time:
48.0	Dynamic Range (dB):
GigE Vision V1.2, GenICam SFNC V1.2.1	Machine Vision Standard:
Electrical	
2.1 (12VDC External Power Supply) 2.4 (PoE)	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power over Ethernet (PoE), via GPIO, or with external power supply	Power Supply:
1 opto-isolated input, 3 opto-isolated outputs	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)	Synchronization:
Back Panel	Interface Port Orientation:
8-pin Hirose (HR25)	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
	Mounting Threads:

Environmental & Durability Factors

+5 to +45	Operating Temperature (°C):
-10 to +70	Storage Temperature (°C):

Regulatory Compliance

Compliant	RoHS 2015:
-----------	------------

View	Certificate of Conformance:
------	-----------------------------

Compliant	Reach 240:
-----------	------------

PRODUCT DETAILS

- Compact, Robust Metal Housing
- One Optocoupled Input, Three Outputs
- Power over Ethernet for Increased Flexibility

Allied Vision Mako Power over Ethernet (PoE) Cameras are ideal digital replacements for analog cameras in a variety of applications, including robots, inspection, or logistics. Allied Vision Mako PoE Cameras feature a precision-aligned sensor to maximize image performance, in addition to a 64MB image buffer. To increase adaptability, Allied Vision Mako PoE Cameras also come equipped with multiple smart features, including the region of interest readout, programmable exposure and white balance, and easy bandwidth control. Allied Vision Mako Power over Ethernet (PoE) Cameras utilize a robust metal housing along with camera temperature monitoring to ensure maximum performance in a range of environments. These cameras are offered in both monochrome and color, with varying resolutions.

Note: GigE cable and power supply (if not using PoE) required for operation.