




NOTES:

1. SUBSTRATE: FUSED SILICA
 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: NONE
 - S2: 352nm Laser AR Coating
 - R(ABS) < 0.25% @ 355nm @ 0° AOI
- DAMAGE THRESHOLD
 PULSED: 7.5J/cm² @ 20ns, 20Hz @ 355nm



 FINE GRIND SURFACE

4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	31.81 x 22.50	Ø22.50
SURFACE FLATNESS	λ/20	λ/20
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE
 PROJECTION



ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

25mm 1/20 WV 355nm AR CTD HT RA FS PRISM

DWG NO

37627

SHEET
 1 OF 1