



FOCAL LENGTH (EFL):  $25 \pm 0,25$   
 BACK FOCAL LENGTH (BFL):  $24,16$

- 1 AR COATING: VIS-EXT  
 $R(\text{AVG}) \leq 0,5\%$  FROM 350-700nm @  $0^\circ$  AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$25,41 \pm 0,025$ CX	GLASS N-BK7 517/642	R	$25,41 \pm 0,025$ CX
$\text{Øe}$	9		$\text{Øe}$	9
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT      SCALE: NONE       $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE: 10mm Dia, x 25mm FL, VIS-EXT Coated, Inked, Double-Convex Lens

DWG NO: 891451NK

SHEET SIZE: A4      SHEET 1 OF 1