


[All Products](#) / [Lasers](#) / [Laser Measurement and Electronics](#) / [Laser Beam Analysis](#)

Coherent® Lasercam™ Beam Profiler

 See More by [Coherent®](#)


- 12 and 14-bit Digital USB 2.0 Interface Options
- High Sensitivity and Dynamic Range
- Intuitive BeamView™ Software Included

Common Specifications

Physical & Mechanical Properties

Dimensions (mm):	68.1 x 79.3 x 40.9 (with LDFP)	Weight (g):	110 (without cable)
Dimensional Accuracy:	±1% (typical), ±5% max (over entire spectral and dimensional range)		

Optical Properties

Peak Intensity:	Recommended: 75-95% of camera saturation
Damage Threshold, By Design:	32 mJ/cm ² @ 1.06μm without Low Distortion Faceplate

Sensor

Gamma:	1.00		
Frame Rate:	27Hz (Live Mode), 10Hz (with calculations)	Exposure Time:	Fixed at 10ms

Electrical

Signal to Noise S/N Ratio (dB):	>60	Gain (dB):	Gain is factory set for optimum linear dynamic range, not user adjustable
--	-----	-------------------	---

Peak Noise (nW/cm²): 24 (at 632.8nm)

Pulse Trigger: TTL, rising or falling edge

Hardware & Interface Connectivity

Operating System: Windows®


Threading & Mounting

Mount: C-Mount


Environmental & Durability Factors

Operating Temperature (°C): -20 to 60

Technical Information



Intuitive Software Interface



Products

Sensor Format	Beam Diameter, 1/e ² (mm)	Sensing Area, H x V (mm)	Stock Number	Price	Buy
1/2"	Recommended: 0.15mm min, 4.0mm max	5.9 x 4.8	#33-156	S\$7,072.01	1 In Stock
2/3"	Recommended: 0.20mm min, 6.0mm max	8.3 x 6.6	#33-157	S\$9,104.55	3 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com