

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Ring Lights](#)

Advanced Illumination Standard Working Distance LED Ring Lights


See More by [Advanced Illumination](#)



- 4" Working Distance
- Provides 1.7" Coverage
- Variable Intensity and Strobed Options

Technical Information

Products

Color	Wavelength (nm)	Dia. (mm)	Illumination Mode	Inner Diameter (mm)	Stock Number	Price	Buy
					#66-774 Clearance		
							
					Clearance		
					Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
White	-	85.00	Constant	55.4		S\$587.18	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com