

[All Products](#) / [Optomechanics](#) / [Tube System](#) / [SM Tube System](#)

TECHSPEC® SM Fine Focus Tubes



- Ideal for Variable Spacing Along the Optical Axis of SM1 or SM05 Systems
- Anti-Reflection Processing for Reduced Stray Light
- Built-in Set Screw for Focus Locking

Common Specifications

General

Function:

Extension Tube (Adjustable)

Physical & Mechanical Properties

Construction:

Anodized Aluminum

Technical Information

Products

Thread Type	Extension Length (mm)	Stock Number	Price	Buy
1.035 x 40 TPI (SM1)	20.0 - 30.0	#35-762	S\$76.91	12 In Stock
0.535 x 40 TPI (SM05)	13.5 - 17.0	#35-783	S\$76.91	4 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com