

[All Products](#) / [Lasers](#) / [Laser Measurement and Electronics](#) / [Laser Power Meters](#)

Coherent® Fan-Cooled Thermopile Sensors See More by [Coherent®](#)



- Designed to Measure Laser Power up to 300W
- Ideal for Applications where Water-Cooling is Not Possible
- Compact Size for Portability and Use in Field Applications

Common Specifications

General

Calibration Uncertainty (%):	1	Cooling Method:	Fan
Compatible Meters:	#35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412		

Physical & Mechanical Properties

Active Area Diameter (mm):	50
----------------------------	----

Optical Properties

Calibration Wavelength (nm):	514	Wavelength Range (nm):	250 - 11000
Wavelength Range (µm):	0.25-11		

Electrical

Power Resolution (W):	0.1
Minimum Power (W):	1

Hardware & Interface Connectivity

Computer Interface:	DB-25
---------------------	-------

Technical Information

Products

Power Range	Power Resolution (W)	Wavelength Range (nm)	Active Area Diameter (mm)	Cooling Method	Model Number	Stock Number	Price	Buy
1W-200W	0.1	250 - 11000	50	Fan	1098472	#12-402	S\$3,690.25	3 In Stock
1W-300W	0.1	250 - 11000	50	Fan	1098417	#12-405	S\$3,886.00	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100
[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :
www.edmundoptics.com