

[All Products](#) / [Lasers](#) / [Laser Mechanics](#)

ScannerMAX Compact 506 Dual Axis Galvanometer

Optical Scanners

See More by [ScannerMAX](#)



- 3, 5, and 10mm Mirror Apertures
- Dual Axis Configuration with Protected Silver Coating
- Compact, Light-Weight, Low-Cost Scanners
- [High Performance ScannerMAX Saturn Scanners](#) Also Available

Common Specifications

General			
Model Number:		ScannerMAX Compact 506	
Physical & Mechanical Properties			
Rotor Inertia (gm-cm ²):		0.014	
Torque Constant (dyne-cm/A):		18,400	
Optical Properties			
Surface Flatness (P-V):		≤λ/4 @ 632.8nm	
Coating: Protected Silver		Substrate: Silicon (Si)	
Electrical			
Position Signal (V): ±10		Current - Peak (A): Maximum: 10	
Current - RMS (A): 1.85 (Case @ 50°C)		Coil Resistance (Ω): 1.8	
Coil Inductance (μH): 280		Back EMF Voltage (μV/°/s): 32.1	
Hardware & Interface Connectivity			
Power Requirement: ±24 VDC		Power Supply: 1 x #16-045 Europe (CE Marked): 2 x #14-571	
Environmental & Durability Factors			
Operating Temperature (°C):		0 to +50	

Technical Information

Products

Title	Stock Number	Price	Buy
3mm Aperture, Protected Silver, Compact 506 Dual Axis Galvanometer Scanner	#16-036	S\$3,915.00	3 In Stock
5mm Aperture, Protected Silver, Compact 506 Dual Axis Galvanometer Scanner	#16-037	S\$3,625.00	2 In Stock
10mm Aperture, Protected Silver, Compact 506 Dual Axis Galvanometer Scanner	#16-038	S\$4,060.00	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com